



## Softcare Antistatic 300 ml

Softcare Antistatic effectively removes static electricity from various textile, glass and plastic surfaces. The effect lasts for several weeks, even months. Static electricity causes dust to collect and unpleasant electric shock. By treating your furniture with Softcare Antistatic, you keep them free from static electricity even for months. Renew treatment when necessary. Easy to use and effective; long-lasting protection against static electricity.

**Instructions for use:** Spray evenly and lightly on the surface from a 15-20 cm distance. Ensure good ventilation and protect delicate surfaces. Test the colour's durability on an invisible place. Package contains 300 ml Softcare Antistatic sufficient for approximately 10-20 m<sup>2</sup>.

**Usage:** Spray surface evenly and let dry 2 h in room temperature before use. Perform treatment in a well ventilated area or outdoors. Repeat treatment when necessary. Not suitable for faux leather or plastic.



VAARA / FARA /  
DANGER / OHT

### WARNINGS AND ADDITIONAL INFORMATION

ISOPROPYL ALCOHOL (CAS 67-63-0). Highly flammable liquid and vapour. Causes serious eye irritation. May cause drowsiness or dizziness. Keep out of reach of children. Keep away from open flames. - No smoking. Avoid breathing spray. Use only outdoors or in a well-ventilated area. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: get medical attention. Dispose of contents to hazardous waste collection point.

**Safety data sheets:** [Download PDF](#) (in Finnish)

**Volume:** 300ml

**EAN:** 6416977712527

<https://www.softcare.fi/en/product/softcare-antistatic-300-ml/>